


## Ultrasonic distance measuring sensors

## UNDK 10 (Sd = 200 mm)

### sample drawing



### general data

scanning range sd	20 ... 200 mm
scanning range close limit Sdc	20 ... 200 mm
scanning range far limit Sde	20 ... 200 mm
repeat accuracy	< 0,5 mm
resolution	< 0,3 mm
adjustment	Teach-in
sonic frequency	380 kHz
response time ton	< 60 ms
release time toff	< 60 ms
alignment aid	target indication flashing
light indicator	yellow LED / red LED
temperature drift	< 2 % of distance to target So

### electrical data

voltage supply range +Vs	15 ... 30 VDC
current consumption max.	35 mA
output circuit	voltage output
output signal	0 ... 10 V / 10 ... 0 V
output current	< 20 mA
residual ripple	< 10 % Vs
short circuit protection	yes
reverse polarity protection	yes

### mechanical data

type	rectangular
housing material	plastic (ASA)
width / diameter	10,4 mm
height / length	27 mm
depth	14 mm

### ambient conditions

operating temperature	-10 ... +60 °C
protection class	IP 67

### sample picture



**Ultrasonic distance measuring  
sensors****UNDK 10 (Sd = 200 mm)**

<b>order reference</b>	<b>connection types</b>
<b>UNDK 10U6914</b>	cable PUR 4 x 0,08, 2 m
<b>UNDK 10U6914/KS35A</b>	flylead connector M8, L=200 mm
<b>UNDK 10U6914/S35A</b>	connector M8